



Fan Heater 230 Volt 16 Cubic Feet Per Minute 125 Watts

By Wiegmann
Catalog # [FH230V125W](#)

Fan Heater 230 Volt 16 Cubic Feet Per Minute 125 Watts



*Representative Image

Features

- Built in adjustable thermostat
- Auto fan control switch
- Integrated overheat protection

Application

Heating

General

Color	Silver
EU RoHS Indicator	No
Material	Stainless Steel
Type	Fan Heater
UPC	786725885978

Dimensions

Actual Depth	4.5 in
Actual Height	5.4 in
Actual Width	4.1 in
Depth	5 in
Height	6 in
Width	4 in

Electrical Ratings

Voltage Rating	230 V
Wattage	125 W

Certifications and Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

Logistics

Carton Quantity	60
-----------------	----

Product Assets

[Brochures - Environmental Controls - Thermal Products](#)
[Catalogs - Wiegmann Environmental Controls](#)
[Engineering Drawing - FH115V125W-FH230V200W](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-FH230V125W-SPEC-EN | REV 1/2024