



# Fan Heater 230 Volt 20 Cubic Feet Per Minute 250 Watts

By Wiegmann  
Catalog # [FH230V250W](#)

Fan Heater 230 Volt 20 Cubic Feet Per Minute 250 Watts



\*Representative Image

## Features

- Available in 115V or 230V
- Supplied with DIN rail clip installed
- Connection is a 3 screw terminal for 14 AWG

## Application

Heating

## General

Color	Gray
EU RoHS Indicator	No
Material	Plastic
Type	Fan Heater
UPC	786725886067

## Dimensions

Actual Depth	3.2 in
Actual Height	5.3 in
Actual Width	4.4 in
Depth	3 in
Height	5 in
Width	4 in

## Electrical Ratings

Voltage Rating	230 V
Wattage	250 W

## Certifications and Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

[Brochures - Environmental Controls - Thermal Products](#)  
[Catalogs - Wiegmann Environmental Controls](#)  
[Engineering Drawing - FHseries](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WIEG-FH230V250W-SPEC-EN | REV 1/2024