



# Fan Heater 230 Volt 20 Cubic Feet Per Minute 400 Watts

By Wiegmann  
Catalog # [FH230V400W20](#)

Fan Heater 230 Volt 20 Cubic Feet Per Minute 400 Watts



\*Representative Image

## Features

- Available in 115V or 230V
- Supplied with DIN rail clip installed
- Connection is a 3 screw terminal for 14 AWG

## Application

Heating

## General

Catalog Number	FH230V400W20
Color	Gray
EU RoHS Indicator	No
Material	Plastic
Type	Fan Heater
UPC	786725886081

## Dimensions

Actual Depth	3.2 in
Actual Height	6.5 in
Actual Width	4.4 in

Depth	3 in
Height	7 in
Width	4 in

## Electrical Ratings

Voltage Rating	230 V
Wattage	400 W

## Certifications And Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

- [Brochures - Environmental Controls - Thermal Products](#)
- [Catalogs - Wiegmann Environmental Controls](#)
- [Engineering Drawing - FHseries](#)
- [SDS - HCC SDS](#)
- [Specifications - FH230V400W20](#)
- [Terms and Conditions - HCC Terms & Conditions](#)