



# NEMA 4X Continuous Hinge Two Screw Cover 14X12X8 Fiberglass-Opaque

By Wiegmann  
Catalog # [HW-141208CHSC](#)

NEMA 4X Continuous Hinge Two Screw Cover 14X12X8  
Fiberglass-Opaque



\*Representative Image

## Features

- Constructed of molded fiberglass
- Continuous hinge with two-screw cover
- Poured seamless gasket provides a water-tight and dust-tight seal
- Optional mounting foot kit is available

## General

Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Premier
Type	Enclosure
UPC	786725856060

## Dimensions

Cubic Capacity	1344 cu.in
Depth	8 in
Height	14 in
Weight	9.5 lb
Width	12 in

## Certifications and Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

- [3D Models - HW-141208CHSC](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-141208CHSC-S](#)
- [SDS - HCC\\_SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WIEG-HW-141208CHSC-SPEC-EN | REV 7/2023