



# NEMA 4X Continuous Hinge Quick Release Padlockable With Window 14X12X8 Fiberglass-Opaque

By Wiegmann  
Catalog # [HW-141208CHQRW](#)

NEMA 4X Continuous Hinge Quick Release Padlockable With Window 14X12X8 Fiberglass-Opaque



\*Representative Image

## Features

- Constructed of molded fiberglass
- Windowed cover with continuous hinge and quick-release padlockable latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Optional mounting foot kit is available

## General

Color	Gray
Cover Type	Hinged Cover with Window
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Premier
Type	Enclosure
UPC	786725879830

## Dimensions

Cubic Capacity	1344 cu.in
Depth	8 in
Height	14 in
Weight	12.2 lb
Width	12 in

## Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

## Logistics

Carton Quantity 1

## Product Assets

- [3D Models - HW-141208CHQRW](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-141208CHQRW-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand