

**NEMA 4X Continuous Hinge Two  
Screw Cover 14X12X8 Fiberglass-  
Opaque**

By Wiegmann  
Catalog # [HW-141208CHSC](#)

NEMA 4X Continuous Hinge Two Screw Cover 14X12X8  
Fiberglass-Opaque

**Features**

- Constructed of molded fiberglass
- Continuous hinge with two-screw cover
- Poured seamless gasket provides a water-tight and dust-tight seal
- Optional mounting foot kit is available

**General**

Catalog Number	HW-141208CHSC
Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Premier
Type	Enclosure
UPC	786725856060

**Dimensions**

Cubic Capacity	1344 cu.in
----------------	------------



\*Representative Image

Depth	8 in
Height	14 in
Weight	9.5 lb
Width	12 in

**Certifications And Compliance**

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

**Logistics**

Carton Quantity	1
-----------------	---

**Product Assets**

[3D Models - HW-141208CHSC](#)  
[Catalogs - Wiegmann Non-Metallic Enclosures](#)  
[Engineering Drawing - HWDHW-141208CHSC-S](#)  
[SDS - HCC SDS](#)  
[Specifications - HW-141208CHSC](#)  
[Terms and Conditions - HCC Terms & Conditions](#)