



NEMA 4X Continuous Hinge Two Screw Cover 14X12X8 Fiberglass- Opaque

By Wiegmann
Catalog # [HW-141208CHSC](#)

NEMA 4X Continuous Hinge Two Screw Cover 14X12X8
Fiberglass-Opaque



*Representative Image

Features

- Constructed of molded fiberglass
- Continuous hinge with two-screw cover
- Poured seamless gasket provides a water-tight and dust-tight seal
- Optional mounting foot kit is available

General

Catalog Number	HW-141208CHSC
Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Premier
Type	Enclosure
UPC	786725856060

Dimensions

Cubic Capacity	1344 cu.in
Depth	8 in
Height	14 in
Weight	9.5 lb
Width	12 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity 1

Product Assets

- [3D Models - HW-141208CHSC](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-141208CHSC-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand