



NEMA 4X Continuous Hinge Quick Release Padlockable With Window 16X14X8 Fiberglass-Opaque

By Wiegmann
Catalog # [HW-161408CHQRW](#)

NEMA 4X Continuous Hinge Quick Release Padlockable With Window 16X14X8 Fiberglass-Opaque



*Representative Image

Features

- Constructed of molded fiberglass
- Windowed cover with continuous hinge and quick-release padlockable latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Optional mounting foot kit is available

General

Color	Gray
Cover Type	Hinged Cover with Window
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Premier
Type	Enclosure
UPC	786725879847

Dimensions

Cubic Capacity	1792 cu.in
Depth	8 in
Height	16 in
Weight	16 lb
Width	14 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity 1

Product Assets

- [3D Models - HW-161408CHQRW](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-161408CHQRW-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand