



# NEMA 4X Continuous Hinge Two Screw Cover 16X14X8 Fiberglass-Clear Cover

By Wiegmann  
Catalog # [HW-CC161408CHSC](#)

NEMA 4X Continuous Hinge Two Screw Cover 16X14X8  
Fiberglass-Clear Cover



\*Representative Image

## Features

- Constructed of molded fiberglass
- Clear cover with continuous hinge and two screws
- Poured seamless gasket provides a water-tight and dust-tight seal
- Optional mounting foot kit is available

## General

Color	Gray
	Clear
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Premier
Type	Enclosure
UPC	786725879762

## Dimensions

Cubic Capacity	1792 cu.in
Depth	8 in
Height	16 in
Weight	13.8 lb
Width	14 in

## Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

## Logistics

Carton Quantity 1

## Product Assets

[3D Models - HW-CC161408CHSC](#)  
[Catalogs - Wiegmann Non-Metallic Enclosures](#)  
[Engineering Drawing - HWDHW-CC161408CHSC-S](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand