



# NEMA 4X JIC Continuous Hinge Link Lock With Window 12X10X5 Fiberglass-Opaque

By Wiegmann  
Catalog # [HW-J121005CHTLW](#)

NEMA 4X JIC Continuous Hinge Link Lock With Window  
12X10X5 Fiberglass-Opaque



\*Representative Image

### Features

- Constructed of molded fiberglass
- Windowed cover with continuous hinge and twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

### General

|                |                          |
|----------------|--------------------------|
| Catalog Number | HW-J121005CHTLW          |
| Color          | Gray                     |
| Cover Type     | Hinged Cover with Window |
| Material       | Fiberglass               |
| Mounting Type  | Wall Mount               |
| Series         | JIC                      |
| Type           | Enclosure                |
| UPC            | 786725857364             |

### Dimensions

|               |          |
|---------------|----------|
| Actual Depth  | 5.21 in  |
| Actual Height | 13.56 in |
| Actual Width  | 11.43 in |

|                |           |
|----------------|-----------|
| Cubic Capacity | 600 cu.in |
| Depth          | 5 in      |
| Height         | 12 in     |
| Weight         | 6.5 lb    |
| Width          | 10 in     |

### Certifications And Compliance

|                        |                      |
|------------------------|----------------------|
| Buy American Compliant | Contact Manufacturer |
| Certified Listed       | cULus                |
| Nema Rating            | 4X                   |
| UL Listed              | Yes                  |

### Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

### Product Assets

- [3D Models - HW-J121005CHTLW](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-J121005CHTLW-S](#)
- [SDS - HCC SDS](#)
- [Specifications - HW-J121005CHTLW](#)
- [Terms and Conditions - HCC Terms & Conditions](#)