



NEMA 4X JIC Continuous Hinge Quick Release Padlockable With Window 14X12X6 Fiberglass- Opaque

By Wiegmann
Catalog # [HW-J141206CHQRW](#)



*Representative Image

NEMA 4X JIC Continuous Hinge Quick Release Padlockable With Window 14X12X6 Fiberglass-Opaque

Features

- Constructed of molded fiberglass
- Windowed cover with continuous hinge and quick-release padlockable latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Catalog Number	HW-J141206CHQRW
Color	Gray
Cover Type	Hinged Cover with Window
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure
UPC	786725857449

Dimensions

Actual Depth	6.25 in
Actual Height	15.5 in
Actual Width	13.5 in
Cubic Capacity	1008 cu.in
Depth	6 in
Height	14 in
Weight	8.5 lb
Width	12 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity 1

Product Assets

- [3D Models - HW-J141206CHQRW](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-J141206CHQRW-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-HWJ141206CHQRW-SPEC-EN | REV 6/2024