



NEMA 4X JIC Continuous Hinge Link Lock With Window 16X14X6 Fiberglass-Opaque

By Wiegmann
Catalog # [HW-J161406CHTLW](#)

NEMA 4X JIC Continuous Hinge Link Lock With Window
16X14X6 Fiberglass-Opaque



*Representative Image

Features

- Constructed of molded fiberglass
- Windowed cover with continuous hinge and twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Catalog Number	HW-J161406CHTLW
Color	Gray
Cover Type	Hinged Cover with Window
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure
UPC	786725857395

Dimensions

Actual Depth	6.23 in
Actual Height	17.53 in
Actual Width	15.46 in

Cubic Capacity	1344 cu.in
Depth	6 in
Height	16 in
Weight	11.5 lb
Width	14 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - HW-J161406CHTLW](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-J161406CHTLW-S](#)
- [SDS - HCC SDS](#)
- [Specifications - HW-J161406CHTLW](#)
- [Terms and Conditions - HCC Terms & Conditions](#)