



NEMA 4X JIC Continuous Hinge Link Lock With Window 18X16X8 Fiberglass-Opaque

By Wiegmann
Catalog # [HW-J181608CHTLW](#)

NEMA 4X JIC Continuous Hinge Link Lock With Window 18X16X8
Fiberglass-Opaque



*Representative Image

Features

- Constructed of molded fiberglass
- Windowed cover with continuous hinge and twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Catalog Number	HW-J181608CHTLW
Color	Gray
Cover Type	Hinged Cover with Window
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure
UPC	786725857401

Dimensions

Actual Depth	8.82 in
Actual Height	19.62 in
Actual Width	17.61 in
Cubic Capacity	2304 cu.in
Depth	8 in
Height	18 in
Weight	19.25 lb
Width	16 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity 1

Product Assets

- [3D Models - HW-J181608CHTLW](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-J181608CHTLW-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-HWJ181608CHTLW-SPEC-EN | REV 6/2024