



# NEMA 4X JIC Continuous Hinge Quick Release Padlockable Extended Depth 8X6X8 Fiberglass- Opaque

By Wiegmann  
Catalog # [HW-J80608XD](#)



\*Representative Image

NEMA 4X JIC Continuous Hinge Quick Release Padlockable  
Extended Depth 8X6X8 Fiberglass-Opaque

## Features

- Constructed of molded fiberglass
- Extended depth enclosure with lift-off four-screw cover
- Poured seamless gasket provides a water-tight and dust-tight seal

## General

Color	Gray
Cover Type	Screw Cover
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure
UPC	786725878239

## Dimensions

Actual Depth	9.06 in
Actual Height	9.63 in
Actual Width	6.85 in
Cubic Capacity	384 cu.in
Depth	8 in
Height	8 in
Weight	5.3 lb
Width	6 in

## Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

## Logistics

Carton Quantity 1

## Product Assets

- [3D Models - HW-J80608XD](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-J80608XD-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WIEG-HWJ80608XD-SPEC-EN | REV 6/2024