



NEMA 4X JIC Continuous Hinge Link Lock 8X8X4 Fiberglass- Opaque

By Wiegmann
Catalog # [HW-J80804CHTL](#)

NEMA 4X JIC Continuous Hinge Link Lock 8X8X4 Fiberglass- Opaque



*Representative Image

Features

- Constructed of molded fiberglass
- Continuous hinge with twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Color	Gray
Cover Type	Hinged Cover
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure
UPC	786725877133

Dimensions

Actual Depth	4.87 in
Actual Height	9.56 in
Actual Width	9.38 in
Cubic Capacity	256 cu.in
Depth	4 in
Height	8 in
Weight	3.8 lb
Width	8 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity 1

Product Assets

- [3D Models - HW-J80804CHTL](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-J80804CHTL-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-HWJ80804CHTL-SPEC-EN | REV 6/2024