



NEMA 4X JIC Continuous Hinge Quick Release Padlockable Extended Depth 8X8X8 Fiberglass-Opaque

By Wiegmann
Catalog # [HW-J80808XD](#)



*Representative Image

NEMA 4X JIC Continuous Hinge Quick Release Padlockable
Extended Depth 8X8X8 Fiberglass-Opaque

Features

- Constructed of molded fiberglass
- Extended depth enclosure with lift-off four-screw cover
- Poured seamless gasket provides a water-tight and dust-tight seal

General

Color	Gray
Cover Type	Screw Cover
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure
UPC	786725878246

Dimensions

Actual Depth	9.44 in
Actual Height	9.56 in
Actual Width	8.84 in
Cubic Capacity	512 cu.in
Depth	8 in
Height	8 in
Weight	5.8 lb
Width	8 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity 1

Product Assets

- [3D Models - HW-J80808XD](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-J80808XD-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-HWJ80808XD-SPEC-EN | REV 6/2024