



NEMA 4X Continuous Hinge Twist Latch 24X20X8 With Window Fiberglass-Opaque

By Wiegmann
Catalog # [HW-N4X242008CHW](#)

NEMA 4X Continuous Hinge Twist Latch 24X20X8 With Window
Fiberglass-Opaque



*Representative Image

Features

- Constructed of molded fiberglass
- Windowed cover with continuous hinge and twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Color	Gray
Cover Type	Hinged Cover with Window
Material	Fiberglass
Mounting Type	Wall Mount
Series	Control
Type	Enclosure
UPC	786725878345

Dimensions

Cubic Capacity	3840 cu.in
Depth	8 in
Height	24 in
Weight	52.2 lb
Width	20 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - HW-N4X242008CHW](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-N4X242008CHW-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand