



NEMA 4X Continuous Hinge Twist Latch 60X60X24 Fiberglass- Opaque

By Wiegmann
Catalog # [HW-N4X606024CH](#)

NEMA 4X Continuous Hinge Twist Latch 60X60X24 Fiberglass- Opaque

Features

- Constructed of molded fiberglass
- Continuous hinge with twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Catalog Number	HW-N4X606024CH
Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Control
Type	Enclosure
UPC	786725878789

Dimensions

Actual Depth	25.51 in
Actual Height	60.5 in
Actual Width	60.5 in



*Representative Image

Cubic Capacity	96746 cu.in
Depth	26 in
Height	61 in
Weight	460 lb
Width	61 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - HW-N4X606024CH](#)
- [Catalogs - Section F Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-N4X606024CH-S](#)
- [SDS - HCC SDS](#)
- [Specifications - HWN4X606024CH](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand