



NEMA 4X Continuous Hinge Twist Latch 72X60X18 Fiberglass-Opaque

By Wiegmann
Catalog # [HW-N4X726018CH](#)

NEMA 4X Continuous Hinge Twist Latch 72X60X18 Fiberglass-Opaque



*Representative Image

Features

- Constructed of molded fiberglass
- Continuous hinge with twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Control
Type	Enclosure
UPC	786725878840

Dimensions

Actual Depth	13.38 in
Actual Height	72.5 in
Actual Width	60.5 in
Cubic Capacity	57889 cu.in
Depth	13 in
Height	73 in
Weight	415 lb
Width	61 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity 1

Product Assets

- [3D Models - HW-N4X726018CH](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-N4X726018CH-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-HWN4X726018CH-SPEC-EN | REV 6/2024