



NEMA 4X Continuous Hinge Twist Latch 90X72X24 Fiberglass-Opaque

By Wiegmann
Catalog # [HW-N4X907224CH](#)

NEMA 4X Continuous Hinge Twist Latch 90X72X24 Fiberglass-Opaque



*Representative Image

Features

- Constructed of molded fiberglass
- Continuous hinge with twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Color	Gray
Cover Type	Hinged Cover
Material	Fiberglass
Mounting Type	Wall Mount
Series	Control
Type	Enclosure
UPC	786725878932

Dimensions

Actual Depth	25.88 in
Actual Height	90.57 in
Actual Width	72.5 in
Cubic Capacity	172718 cu.in
Depth	26 in
Height	91 in
Weight	765 lb
Width	73 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity 1

Product Assets

- [3D Models - HW-N4X907224CH](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-N4X907224CH-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-HWN4X907224CH-SPEC-EN | REV 6/2024