

NEMA 4X Hinged Extended Depth Screw Cover 12X10X6 Fiberglass- Opaque

By Wiegmann
Catalog # [HW-RHJ121006CHSC](#)

NEMA 4X Hinged Extended Depth Screw Cover 12X10X6
Fiberglass-Opaque

Features

- Constructed of molded fiberglass
- Raised, continuous hinge cover with two screws
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Catalog Number	HW-RHJ121006CHSC
Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure
UPC	786725877836

Dimensions

Cubic Capacity	720 cu.in
----------------	-----------



*Representative Image

Depth	6 in
Height	12 in
Weight	6.7 lb
Width	10 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - HW-RHJ121006CHSC](#)
- [Catalogs - Section F Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-RHJ121006CHSC-S](#)
- [SDS - HCC SDS](#)
- [Specifications - HWRHJ121006CHSC](#)
- [Terms and Conditions - HCC Terms & Conditions](#)