



NEMA 4X Continuous Hinge Quick Release Padlockable Extended Cover With Window 20X16X10 Fiberglass-Opaque

By Wiegmann
Catalog # [HW-RHJ201610CHQRW](#)



*Representative Image

NEMA 4X Continuous Hinge Quick Release Padlockable
Extended Cover With Window 20X16X10 Fiberglass-Opaque

Features

- Constructed of molded fiberglass
- Raised and windowed cover with continuous hinge and quick-release padlockable latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Catalog Number	HW-RHJ201610CHQRW
Color	Gray
Cover Type	Hinged Cover with Window
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure
UPC	786725878222

Dimensions

Cubic Capacity	3200 cu.in
----------------	------------

Depth	10 in
Height	20 in
Weight	21.3 lb
Width	16 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - HW-RHJ201610CHQRW](#)
- [Catalogs - Section F Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-RHJ201610CHQRW-S](#)
- [SDS - HCC SDS](#)
- [Specifications - HWRHJ201610CHQRW](#)
- [Terms and Conditions - HCC Terms & Conditions](#)