



NEMA 4X Hinged Extended Depth Screw Cover 20X16X10 Fiberglass- Opaque

By Wiegmann
Catalog # [HW-RHJ201610CHSC](#)

NEMA 4X Hinged Extended Depth Screw Cover 20X16X10
Fiberglass-Opaque



*Representative Image

Features

- Constructed of molded fiberglass
- Raised, continuous hinge cover with two screws
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure
UPC	786725877874

Dimensions

Cubic Capacity	3200 cu.in
Depth	10 in
Height	20 in
Weight	21 lb
Width	16 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - HW-RHJ201610CHSC](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-RHJ201610CHSC-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand