



# Hygienic Enclosure 24 X 24 X 8, 304 Stainless Steel Sloped-Top

By Wiegmann  
Catalog # [HYG242408SS](#)

Hygienic Enclosure 24 X 24 X 8, 304 Stainless Steel Sloped-Top



## Features

- IP69K Certified Enclosures withstand the rigors or repeated high temperature and high pressure wash down
- The sloped design, gasketed door, and gasketed latching mechanism repel water, chemicals, and debris away from the enclosure.
- Reversible door hardware, pre-drilled mounting holes and optional mounting feet or wall standoffs enable the enclosure to be mounted in the most convenient location possible.

## General

Color	Metallic
Construction	Fully Welded 304 Stainless Steel
Finish Type	Fine Grain Stainless Steel
Material	307 Stainless Steel
Mounting Type	Bolt Direct, Wall Mount foot (optional), Wall Standoff (optional)
Series	Hygienic Series
Size	24 X 24 X 8
Style	Wall Mount
Type	Stainless Steel
UPC	786725891344

## Dimensions

Cubic Capacity	4608 cu.in
Depth	8 in
Height	24 in
Width	24 in

## Certifications and Compliance

Industry Standard(s)

- UL508A Listed
- Types 1, 3R, 4, 4X, 12
- cUL Listed per CSA C22.2 No. 14
- Type 1, 3R, 4, 4X, 12
- NEMA/EEMAC Type 1, 3R, 4, 4X, 12
- IEC 60529 IP69

Nema Rating

NEMA/EEMAC Type 1, 3R, 4, 4X, 12

## Product Assets

[Brochures - IP69 Wash-Down Enclosures for Hygienic Applications](#)  
[Catalogs - Wiegmann Stainless Steel & Aluminium](#)  
[Sell Sheets - IP69 Wash-Down Enclosures for Hygienic Applications Flyer](#)

## Related Products

[HP2424 - Hygienic Series Back Panel 24 X 24, Carbon Steel - White](#)  
[HP2424SS - Hygienic Series Back Panel 24 X 24, 304 Stainless Steel](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WIEG-HYG242408SS-SPEC-EN | REV 1/2024