



Hygienic Enclosure 36 X 24 X 12, 304 Stainless Steel Sloped-Top

By Wiegmann
Catalog # [HYG362412SS](#)



Hygienic Enclosure 36 X 24 X 12, 304 Stainless Steel Sloped-Top

Features

- IP69K Certified Enclosures withstand the rigors or repeated high temperature and high pressure wash down
- The sloped design, gasketed door, and gasketed latching mechanism repel water, chemicals, and debris away from the enclosure.
- Reversible door hardware, pre-drilled mounting holes and optional mounting feet or wall standoffs enable the enclosure to be mounted in the most convenient location possible.

General

Catalog Number	HYG362412SS
Color	Metallic
Construction	Fully Welded 304 Stainless Steel
Finish Type	Fine Grain Stainless Steel
Material	312 Stainless Steel
Mounting Type	Bolt Direct, Wall Mount foot (optional), Wall Standoff (optional)
Series	Hygienic Series
Size	36 X 24 X 12
Style	Wall Mount
Type	Stainless Steel
UPC	786725891399

Dimensions

Cubic Capacity	10368 cu.in
Depth	12 in
Height	36 in
Width	24 in

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• UL508A Listed• Types 1, 3R, 4, 4X, 12• cUL Listed per CSA C22.2 No. 14• Type 1, 3R, 4, 4X, 12• NEMA/EEMAC Type 1, 3R, 4, 4X, 12• IEC 60529 IP69
Nema Rating	NEMA/EEMAC Type 1, 3R, 4, 4X, 12

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Brochures - IP69 Wash-Down Enclosures for Hygienic Applications](#)
- [Catalogs - Section E Stainless Steel & Aluminium](#)
- [Sell Sheets - IP69 Wash-Down Enclosures for Hygienic Applications Flyer](#)
- [Specifications - HYG362412SS](#)
- [Video - Wiegmann - Hygienic Box](#)