



Hygienic Enclosure 36 X 30 X 16, 304 Stainless Steel Sloped-Top

By Wiegmann
Catalog # [HYG363016SS](#)



Hygienic Enclosure 36 X 30 X 16, 304 Stainless Steel Sloped-Top

Features

- IP69K Certified Enclosures withstand the rigors or repeated high temperature and high pressure wash down
- The sloped design, gasketed door, and gasketed latching mechanism repel water, chemicals, and debris away from the enclosure.
- Reversible door hardware, pre-drilled mounting holes and optional mounting feet or wall standoffs enable the enclosure to be mounted in the most convenient location possible.

General

| | |
|----------------|---|
| Catalog Number | HYG363016SS |
| Color | Metallic |
| Construction | Fully Welded 304 Stainless Steel |
| Finish Type | Fine Grain Stainless Steel |
| Material | 315 Stainless Steel |
| Mounting Type | Bolt Direct, Wall Mount foot (optional), Wall Standoff (optional) |
| Series | Hygienic Series |
| Size | 36 X 30 X 16 |
| Style | Wall Mount |
| Type | Stainless Steel |
| UPC | 786725891528 |

Dimensions

| | |
|----------------|-------------|
| Cubic Capacity | 17280 cu.in |
| Depth | 16 in |
| Height | 36 in |
| Width | 30 in |

Certifications And Compliance

| | |
|----------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none">• UL508A Listed• Types 1, 3R, 4, 4X, 12• cUL Listed per CSA C22.2 No. 14• Type 1, 3R, 4, 4X, 12• NEMA/EEMAC Type 1, 3R, 4, 4X, 12• IEC 60529 IP69 |
| Nema Rating | NEMA/EEMAC Type 1, 3R, 4, 4X, 12 |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

Product Assets

- [Brochures - IP69 Wash-Down Enclosures for Hygienic Applications](#)
- [Catalogs - Section E Stainless Steel & Aluminium](#)
- [Sell Sheets - IP69 Wash-Down Enclosures for Hygienic Applications](#)
- [Flyer](#)
- [Specifications - HYG363016SS](#)
- [Video - Wiegmann - Hygienic Box](#)