



N412 Double Door Wall-Mount Ultimate 30X42X10 Stainless Steel

By Wiegmann
 Catalog # [N412D304210SSC](#)



N412 Double Door Wall-Mount Ultimate 30X42X10 Stainless Steel

Features

- Stainless steel construction
- Continuous welded seams
- Doors sealed with poured-in-place gaskets
- Grounding studs welded to doors and body
- Collar studs for mounting optional ULTIMATE series back panels
- 3-point keylocking/padlocking handle included
- NEMA 3R, 4, 4X, 12, 13 and IP66

General

Application	Hubbell Wiegmann N412DSSC Ultimate Series Disconnects are designed to house and protect electrical and electronic components from harsh, dirty environments. For use in installations where dirt, dust, oil, water, or other contaminants are present.
Color	Brushes Stainless Steel
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Smooth Grained Stainless
Knockouts	No
Latches Type	3-Point Handle
Listings	cULus IEC 60529
Material	Stainless Steel
Mounting Type	Mounting Holes Mounting Holes
Number of Doors (Fixed)	2
Number of Holes	4
Series	Ultimate
Sub Brand	Ultimate Series
Type	Enclosure
UPC	786725890514

Dimensions

Cubic Capacity	12600 cu.in
Depth	10 in
Height	30 in
Width	42 in

Conductor Related

Cable Entry	NO
-------------	----

Certifications And Compliance

Certification - CSA Approved	NO
Certification - ETL	NO
Certification - cULus	YES
Certified Listed	cULus IEC
Industry Standard(s)	cULus IEC 60529
Nema Rating	1,3R,12,13,4,4X

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - N412D304210SSC](#)
- [Catalogs - Wiegmann Stainless Steel & Aluminium](#)
- [Engineering Drawing - HWDN412D304210SSC-S](#)
- [Sales Drawings - HWDN412D304210SSC-S](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - N412 ULTIMATE Stainless Steel Series Double Door Enclosure](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-N412D304210SSC-SPEC-EN | REV 6/2024