




N12 22.5 MM 1 Pushbutton Enclosure 3.5X2.7X3.5, 316 Stainless Steel

By Wiegmann
Catalog # [PBGX1SSA](#)

N12 22.5 MM 1 Pushbutton Enclosure 3.5X2.7X3.5, 316 Stainless Steel



*Representative Image

General

Application	Designed to hold all standard brands of miniature 22MM oil-tight pushbuttons, switches and pilot lights. Provides protection from dust, dirt and water. Great for corrosive environments as well.
Construction	Continuously Welded Seams
Cover Type	Pushbutton;Screw
EU RoHS Indicator	Yes
Material	316 Stainless Steel
Mounting Type	External Mounting Plates
Number of Holes	1
Series	PBGX_SSA
Type	Miniature Pushbutton Enclosure
UPC	786725891238

Dimensions

Actual Depth	3.5 in
Actual Height	3.25 in
Actual Width	2.75 in
Depth	4 in
Height	3 in
Weight	2 lb
Width	3 in

Certifications And Compliance

Certified Listed	cULus
Industry Standard(s)	UL508A, Type 4, 4X, 12 & 13 cULus Certified Type 4, 4X, 12 & 13 UL Files E64791
Nema Rating	NEMA Type 4, 4X, 12 and 13
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - PBGX1](#)
- [Catalogs - Wiegmann Operator Interface](#)
- [Catalogs - Wiegmann Stainless Steel & Aluminium](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDPBGX1-S](#)
- [Sales Drawings - HWDPBGX1-S](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Stainless Steel Pushbutton Enclosures](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-PBGX1SSA-SPEC-EN | REV 6/2024