

# N12 22.5 MM 2 Pushbutton Enclosure 5.1X2.7X3.5 316 Stainless Steel

By Wiegmann  
Catalog # [PBGX2SSA](#)

N12 22.5 MM 2 Pushbutton Enclosure 5.1X2.7X3.5 316 Stainless Steel

## Features

- Designed to hold all standard brands of miniature oil-tight pushbuttons, switches and pilot lights
- Provide protection from dust, dirt, oil and water.

## Application

Designed to hold all standard brands of miniature 22MM oil-tight pushbuttons, switches and pilot lights. Provides protection from dust, dirt and water. Great for corrosive environments as well.

## General

Catalog Number	PBGX2SSA
Construction	Continuously Welded Seams
Cover Type	Pushbutton;Screw
EU RoHS Indicator	Yes
Material	316 Stainless Steel
Mounting Type	External Mounting Plates
Number of Holes	2
Series	PBGX_SSA
Type	Miniature Pushbutton Enclosure
UPC	786725891245

## Dimensions

Actual Depth	3.5 in
Actual Height	5.13 in
Actual Width	2.75 in
Depth	4 in



\*Representative Image

Height	5 in
Weight	2 lb
Width	3 in

## Certifications And Compliance

Certified Listed	cULus
Industry Standard(s)	<ul style="list-style-type: none"> <li>UL508A, Type 4, 4X, 12 &amp; 13</li> <li>cULus Certified Type 4, 4X, 12 &amp; 13</li> <li>UL Files E64791</li> </ul>
Nema Rating	NEMA Type 4, 4X, 12 and 13
UL Listed	Yes

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

- [3D Models - PBGX2](#)
- [Catalogs - Section I Operator Interface](#)
- [Catalogs - Section E Stainless Steel & Aluminium](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDPPBGX2-S](#)
- [Sales Drawings - HWDPPBGX2-S](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Stainless Steel Pushbutton Enclosures](#)
- [Specifications - PBGX2SSA](#)
- [Terms and Conditions - HCC Terms & Conditions](#)