



Radiant Heater With Protective Cover 115-230 Volt 150 Watts

By Wiegmann
Catalog # [RHPC115230V150W](#)



Radiant Heater With Protective Cover 115-230 Volt 150 Watts

*Representative Image

Features

- A heat guard is included to protect the heating element
- Heater has a two screw terminal for connection of 14 AWG wire
- DIN rail clip is provided for mounting the heater

Application

Heating

General

Color	Black
Material	Steel
Type	Radiant Heater
UPC	786725885954

Dimensions

Actual Depth	2.48 in
Actual Height	8.66 in
Actual Width	2.76 in
Depth	2 in
Height	9 in
Width	3 in

Electrical Ratings

Voltage Rating	100-240 V
Wattage	150 W

Certifications And Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Brochures - Environmental Controls - Thermal Products](#)
[Catalogs - Wiegmann Environmental Controls](#)
[Engineering Drawing - RHPC_150W](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-RHPC115230V150W-SPEC-EN | REV 6/2024