



# Radiant Heater With Protective Cover 115-230 Volt 25 Watts

By Wiegmann  
Catalog # RHPC115230V25W



Radiant Heater With Protective Cover 115-230 Volt 25 Watts

\*Representative Image

## Features

- Heater is connected using a 20 AWG silicon cable
- DIN Rail clip is provided for mounting the heater

## Application

Heating

## General

|                   |                |
|-------------------|----------------|
| Catalog Number    | RHPC115230V25W |
| Color             | Black          |
| EU RoHS Indicator | No             |
| Material          | Steel          |
| Type              | Radiant Heater |
| UPC               | 786725885916   |

## Dimensions

|               |         |
|---------------|---------|
| Actual Depth  | 1.61 in |
| Actual Height | 4.92 in |
| Actual Width  | 1.61 in |
| Depth         | 2 in    |

|        |      |
|--------|------|
| Height | 5 in |
| Width  | 2 in |

## Electrical Ratings

|                |           |
|----------------|-----------|
| Voltage Rating | 100-240 V |
| Wattage        | 25 W      |

## Certifications And Compliance

|                  |                   |
|------------------|-------------------|
| Certified Listed | UL/cUL Recognized |
|------------------|-------------------|

## Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

## Product Assets

- [Brochures - Environmental Controls - Thermal Products](#)
- [Catalogs - Wiegmann Environmental Controls](#)
- [Engineering Drawing - RHPC\\_25\\_50W](#)
- [SDS - HCC SDS](#)
- [Specifications - RHPC115230V25W](#)
- [Terms and Conditions - HCC Terms & Conditions](#)