



# NEMA 3R Screw Cover Wall Mount 12X12X10 304 Stainless Steel

By Wiegmann  
Catalog # [RSC121210NKSS](#)

NEMA 3R Screw Cover Wall Mount 12X12X10 304 Stainless Steel



\*Representative Image

## Features

- Body and cover are fabricated from 304 stainless steel
- A slip-on reversible cover is securely fastened with screws located along the bottom edge
- Mounting holes are located on the back on the enclosure

## General

Construction	Continuously Welded Seams
Cover Type	Screw Cover
EU RoHS Indicator	No
Knockouts	No
Material	Stainless Steel
Mounting Type	Embossed Mounting Holes
Series	RSC-NKSS
Type	Enclosure
UPC	786725887842

## Dimensions

Cubic Capacity	1440 cu.in
Depth	10 in
Height	12 in
Weight	16 lb
Width	12 in

## Certifications And Compliance

Certified Listed	cULus
Nema Rating	3RX

## Logistics

Carton Quantity 1

## Product Assets

- [3D Models - RSC121210NKSS](#)
- [Brochures - Stainless Steel NEMA 3R Screw Cover Enclosures](#)
- [Catalogs - Wiegmann Stainless Steel & Aluminium](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDRSC121210NKSS-S](#)
- [Sales Drawings - HWDRSC121210NKSS-S](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Stainless Steel NEMA 3RX Screw Cover](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WIEG-RSC121210NKSS-SPEC-EN | REV 6/2024