

**NEMA 3R Screw-Cover Wall-Mount
No Knockouts 12X12X12 Carbon
Steel - Gray**

By Wiegmann
Catalog # [RSC121212NK](#)

NEMA 3R Screw-Cover Wall-Mount No Knockouts 12X12X12
Carbon Steel - Gray

Features

- Body and cover are fabricated from carbon steel
- Slip-on reversible cover is securely fastened with screws located along the bottom edge
- No gasketing is required
- Hasp for padlocking or meter seal is provided

General

Catalog Number	RSC121212NK
Color	Gray
Cover Type	Screw Cover
EU RoHS Indicator	No
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Wall Mount
Series	RSC
Type	Enclosure
UPC	786725880171

Dimensions

Actual Depth	12.07 in
Actual Height	12.13 in



*Representative Image

Actual Width	12.13 in
Cubic Capacity	1728 cu.in
Depth	12 in
Height	12 in
Weight	13 lb
Width	12 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus
Nema Rating	1, 3R

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Catalogs - Section B NEMA 3R Enclosures](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Sales Drawings - HWDRSC121212-S](#)
[SDS - HCC SDS](#)
[Specifications - RSC121212NK](#)
[Terms and Conditions - HCC Terms & Conditions](#)