



NEMA 3R Screw-Cover Wall-Mount No Knockouts 24X24X10 Carbon Steel - Gray

By Wiegmann
Catalog # [RSC242410NK](#)

NEMA 3R Screw-Cover Wall-Mount No Knockouts 24X24X10
Carbon Steel - Gray



*Representative Image

Features

- Body and cover are fabricated from carbon steel
- Slip-on reversible cover is securely fastened with screws located along the bottom edge
- No gasketing is required
- Hasp for padlocking or meter seal is provided

General

Color	Gray
Cover Type	Screw Cover
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Wall Mount
Series	RSC
Type	Enclosure
UPC	786725880058

Dimensions

Actual Depth	10.07 in
Actual Height	24.13 in
Actual Width	24.13 in
Cubic Capacity	5760 cu.in
Depth	10 in
Height	24 in
Weight	49 lb
Width	24 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 3R

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Catalogs - Wiegmann NEMA 3R Enclosures](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-RSC242410NK-SPEC-EN | REV 1/2024