



NEMA 3R Screw Cover Wall Mount 24X36X12 304 Stainless Steel

By Wiegmann
Catalog # [RSC243612NKSS](#)

NEMA 3R Screw Cover Wall Mount 24X36X12 304 Stainless Steel



*Representative Image

Features

- Body and cover are fabricated from 304 stainless steel
- A slip-on reversible cover is securely fastened with screws located along the bottom edge
- Mounting holes are located on the back on the enclosure

General

Construction	Continuously Welded Seams
Cover Type	Screw Cover
EU RoHS Indicator	No
Knockouts	No
Material	Stainless Steel
Mounting Type	Embossed Mounting Holes
Series	RSC-NKSS
Type	Enclosure
UPC	786725888030

Dimensions

Cubic Capacity	10368 cu.in
Depth	12 in
Height	36 in
Weight	102 lb
Width	24 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	3RX

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - RSC243612NKSS](#)
- [Brochures - Stainless Steel NEMA 3R Screw Cover Enclosures](#)
- [Catalogs - Wiegmann Stainless Steel & Aluminium](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDRSC243612NKSS-S](#)
- [Sales Drawings - HWDRSC243612NKSS-S](#)
- [SDS - HCC_SDS](#)
- [Sell Sheets - Stainless Steel NEMA 3RX Screw Cover](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-RSC243612NKSS-SPEC-EN | REV 1/2024