



NEMA 3R Screw-Cover Wall-Mount No Knockouts 36X36X18 Carbon Steel - Galvanized

By Wiegmann
Catalog # [RSC363618GNK](#)

NEMA 3R Screw-Cover Wall-Mount No Knockouts 36X36X18
Carbon Steel - Galvanized



*Representative Image

Features

- Body and cover are fabricated from galvanized steel
- Slip-on reversible cover is securely fastened with screws located along the bottom edge
- No gasketing is required
- Hasp for padlocking or meter seal is provided

General

Color	Gray
Cover Type	Screw Cover
Finish Type	Galvanized
Material	Steel
Mounting Type	Wall Mount
Series	RSC
Type	Enclosure
UPC	786725883936

Dimensions

Actual Depth	18.07 in
Actual Height	36.13 in
Actual Width	36.19 in
Cubic Capacity	23328 cu.in
Depth	18 in
Height	36 in
Weight	62 lb
Width	36 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 3R

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Catalogs - Wiegmann NEMA 3R Enclosures](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-RSC363618GNK-SPEC-EN | REV 1/2024