



# NEMA 3R Screw-Cover Wall-Mount No Knockouts 48X48X12 Carbon Steel - Galvanized

By Wiegmann  
Catalog # [RSC484812GNK](#)

NEMA 3R Screw-Cover Wall-Mount No Knockouts 48X48X12  
Carbon Steel - Galvanized



\*Representative Image

## Features

- Body and cover are fabricated from galvanized steel
- Slip-on reversible cover is securely fastened with screws located along the bottom edge
- No gasketing is required
- Hasp for padlocking or meter seal is provided

## General

Color	Gray
Cover Type	Screw Cover
Finish Type	Galvanized
Material	Steel
Mounting Type	Wall Mount
Series	RSC
Type	Enclosure
UPC	786725883950

## Dimensions

Actual Depth	12.07 in
Actual Height	48.13 in
Actual Width	48.19 in
Cubic Capacity	27648 cu.in
Depth	12 in
Height	48 in
Weight	70 lb
Width	48 in

## Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 3R

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

[Catalogs - Wiegmann NEMA 3R Enclosures](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WIEG-RSC484812GNK-SPEC-EN | REV 1/2024