



NEMA 3R Screw-Cover Wall-Mount No Knockouts 48X48X12 Carbon Steel - Gray

By Wiegmann
Catalog # [RSC484812NK](#)

NEMA 3R Screw-Cover Wall-Mount No Knockouts 48X48X12
Carbon Steel - Gray



*Representative Image

Features

- Body and cover are fabricated from carbon steel
- Slip-on reversible cover is securely fastened with screws located along the bottom edge
- No gasketing is required
- Hasp for padlocking or meter seal is provided

General

Color	Gray
Cover Type	Screw Cover
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Wall Mount
Series	RSC
Type	Enclosure
UPC	786725883967

Dimensions

Actual Depth	12.07 in
Actual Height	48.13 in
Actual Width	48.19 in
Cubic Capacity	27648 cu.in
Depth	12 in
Height	48 in
Weight	70 lb
Width	48 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	1, 3R

Logistics

Carton Quantity 1

Product Assets

[Catalogs - Wiegmann NEMA 3R Enclosures](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-RSC484812NK-SPEC-EN | REV 6/2024