




NEMA 3R Gutter 4X4X18 Carbon Steel - Galvanized

By Wiegmann
Catalog # [RSCG040418G](#)



NEMA 3R Gutter 4X4X18 Carbon Steel - Galvanized

*Representative Image

Features

- Trough and cover are fabricated from galvanized steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge
- Knockouts are located on the bottom of the enclosure

General

Color	Gray
Cover Type	Screw Cover
EU RoHS Indicator	No
Finish Type	Galvanized
Knockouts	Yes
Material	Steel
Mounting Type	Wall Mount
Series	RSCG
Type	Gutter
UPC	786725884049

Dimensions

Actual Depth	4.06 in
Actual Height	4.06 in
Actual Width	18.13 in
Depth	4 in
Height	4 in
Width	18 in

Conductor Related

Cable Entry	Knock Outs
-------------	------------

Certifications And Compliance

Certified Listed	cULus
Nema Rating	1, 3R

Logistics

Carton Quantity	4
-----------------	---

Product Assets

- [Catalogs - Wiegmann Wireways & Fittings](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-RSCG040418G-SPEC-EN | REV 6/2024