



# NEMA 3R Gutter - No Knockouts 4X4X18 Carbon Steel - Gray

By Wiegmann  
Catalog # [RSCG040418NK](#)



NEMA 3R Gutter - No Knockouts 4X4X18 Carbon Steel - Gray

\*Representative Image

## Features

- Trough and cover are fabricated from carbon steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge

## General

Color	Gray
Cover Type	Screw Cover
EU RoHS Indicator	No
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Wall Mount
Series	RSCG
Type	Gutter
UPC	786725884063

## Dimensions

Actual Depth	4.06 in
Actual Height	4.06 in
Actual Width	18.13 in
Depth	4 in
Height	4 in
Width	18 in

## Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 3R

## Logistics

Carton Quantity	4
-----------------	---

## Product Assets

[Catalogs - Wiegmann Wireways & Fittings](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WIEG-RSCG040418NK-SPEC-EN | REV 1/2024