



NEMA 3R Gutter - No Knockouts 4X4X96 Carbon Steel - Gray

By Wiegmann
Catalog # [RSCG040496NK](#)



NEMA 3R Gutter - No Knockouts 4X4X96 Carbon Steel - Gray

*Representative Image

Features

- Trough and cover are fabricated from carbon steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge

General

Color	Gray
Cover Type	Screw Cover
EU RoHS Indicator	No
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Wall Mount
Series	RSCG
Type	Gutter
UPC	786725884100

Dimensions

Actual Depth	4.06 in
Actual Height	4.06 in
Actual Width	96.13 in
Depth	4 in
Height	4 in
Width	96 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 3R

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Catalogs - Wiegmann Wireways & Fittings](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-RSCG040496NK-SPEC-EN | REV 1/2024