



NEMA 3R Gutter - No Knockouts 12X12X96 Carbon Steel - Galvanized

By Wiegmann
Catalog # [RSCG121296GNK](#)



NEMA 3R Gutter - No Knockouts 12X12X96 Carbon Steel -
Galvanized

*Representative Image

Features

- Trough and cover are fabricated from galvanized steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge

General

Color	Gray
Cover Type	Screw Cover
Finish Type	Galvanized
Material	Steel
Mounting Type	Wall Mount
Series	RSCG
Type	Gutter
UPC	78672588351

Dimensions

Actual Depth	12.06 in
Actual Height	12.06 in
Actual Width	96.13 in
Depth	12 in
Height	12 in
Width	96 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 3R

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Catalogs - Wiegmann Wireways & Fittings](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-RSCG121296GNK-SPEC-EN | REV 1/2024