



# NEMA 4X Hinge Cover Wire Trough 2.5 X 2.5 X 18 in. 304 Stainless Steel

By Wiegmann  
Catalog # T2218CHSS



NEMA 4X Hinge Cover Wire Trough 2.5 X 2.5 X 18 in. 304 Stainless Steel

\*Representative Image

## Features

- Trough and cover are fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Easy to operate external clamps and continuous hinge are provided
- External mounting feet are included
- Cover is sealed with a poured in place gasket

## General

Cover Type	Hinged Cover
EU RoHS Indicator	No
Finish Type	Grained Stainless Steel
Latches Type	External Clamps
Material	304 Stainless Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Series	T_CHSS
UPC	786725888511

## Dimensions

Actual Depth	18.31 in
Actual Height	4 in
Actual Width	4 in
Depth	18 in
Height	2.5 in
Weight	6.5 lb
Width	2.5 in

## Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 12, 4 & 4X

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

- [3D Models - T2218CHSS](#)
- [Catalogs - Wiegmann Wireways & Fittings](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDT2218CHSS-S](#)
- [Sales Drawings - HWDT2218CHSS-S](#)
- [SDS - HCC\\_SDS](#)
- [Sell Sheets - T-CHSS Series Stainless Steel Wiring Trough](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WIEG-T2218CHSS-SPEC-EN | REV 1/2024