



## NEMA 4X Hinge Cover Wire Trough 4 X 4 X 72 in. 304 Stainless Steel

By Wiegmann  
Catalog # [T4472CHSS](#)



NEMA 4X Hinge Cover Wire Trough 4 X 4 X 72 in. 304 Stainless Steel

\*Representative Image

### Features

- Trough and cover are fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Easy to operate external clamps and continuous hinge are provided
- External mounting feet are included
- Cover is sealed with a poured in place gasket

### General

Cover Type	Hinged Cover
Finish Type	Grained Stainless Steel
Latches Type	External Clamps
Material	304 Stainless Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Series	T_CHSS
UPC	786725888641

### Dimensions

Actual Depth	72.31 in
Actual Height	5.5 in
Actual Width	5.5 in
Depth	72 in
Height	4 in
Weight	30.5 lb
Width	4 in

### Certifications And Compliance

Certified Listed	cULus
Nema Rating	1, 12, 4 & 4X

### Logistics

Carton Quantity 1

### Product Assets

- [3D Models - T4472CHSS](#)
- [Catalogs - Wiegmann Wireways & Fittings](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDT4472CHSS-S](#)
- [Sales Drawings - HWDT4472CHSS-S](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - T-CHSS Series Stainless Steel Wiring Trough](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WIEG-T4472CHSS-SPEC-EN | REV 6/2024