



NEMA 4X Hinge Cover Wire Trough 6 X 6 X 12 in. 304 Stainless Steel

By Wiegmann
Catalog # [T6612CHSS](#)



NEMA 4X Hinge Cover Wire Trough 6 X 6 X 12 in. 304 Stainless Steel

*Representative Image

Features

- Trough and cover are fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Easy to operate external clamps and continuous hinge are provided
- External mounting feet are included
- Cover is sealed with a poured in place gasket

General

Cover Type	Hinged Cover
Finish Type	Grained Stainless Steel
Latches Type	External Clamps
Material	304 Stainless Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Series	T_CHSS
UPC	786725888658

Dimensions

Actual Depth	12.31 in
Actual Height	7.5 in
Actual Width	7.5 in
Depth	12 in
Height	6 in
Weight	10.2 lb
Width	6 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	1, 12, 4 & 4X

Logistics

Carton Quantity 1

Product Assets

- [3D Models - T6612CHSS](#)
- [Catalogs - Wiegmann Wireways & Fittings](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDT6612CHSS-S](#)
- [Sales Drawings - HWDT6612CHSS-S](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - T-CHSS Series Stainless Steel Wiring Trough](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-T6612CHSS-SPEC-EN | REV 6/2024