



NEMA 4X Hinge Cover Wire Trough 6 X 6 X 30 in. 304 Stainless Steel

By Wiegmann
Catalog # T6630CHSS



NEMA 4X Hinge Cover Wire Trough 6 X 6 X 30 in. 304 Stainless Steel

*Representative Image

Features

- Trough and cover are fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Easy to operate external clamps and continuous hinge are provided
- External mounting feet are included
- Cover is sealed with a poured in place gasket

General

Cover Type	Hinged Cover
Finish Type	Grained Stainless Steel
Latches Type	External Clamps
Material	304 Stainless Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Series	T_CHSS
UPC	786725888689

Dimensions

Actual Depth	30.31 in
Actual Height	7.5 in
Actual Width	7.5 in
Depth	30 in
Height	6 in
Weight	20.5 lb
Width	6 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 12, 4 & 4X

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[3D Models - T6630CHSS](#)
[Catalogs - Wiegmann Wireways & Fittings](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - HWDT6630CHSS-S](#)
[Sales Drawings - HWDT6630CHSS-S](#)
[SDS - HCC_SDS](#)
[Sell Sheets - T-CHSS Series Stainless Steel Wiring Trough](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-T6630CHSS-SPEC-EN | REV 1/2024