



# NEMA 4X Hinge Cover Wire Trough 6 X 6 X 48 in. 304 Stainless Steel

By Wiegmann  
Catalog # T6648CHSS



NEMA 4X Hinge Cover Wire Trough 6 X 6 X 48 in. 304 Stainless Steel

\*Representative Image

## Features

- Trough and cover are fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Easy to operate external clamps and continuous hinge are provided
- External mounting feet are included
- Cover is sealed with a poured in place gasket

## General

Cover Type	Hinged Cover
EU RoHS Indicator	No
Finish Type	Grained Stainless Steel
Latches Type	External Clamps
Material	304 Stainless Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Series	T_CHSS
UPC	786725888702

## Dimensions

Actual Depth	48.31 in
Actual Height	7.5 in
Actual Width	7.5 in
Depth	48 in
Height	6 in
Weight	30.7 lb
Width	6 in

## Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 12, 4 & 4X

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

[3D Models - T6648CHSS](#)  
[Catalogs - Wiegmann Wireways & Fittings](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Engineering Drawing - HWDT6648CHSS-S](#)  
[Sales Drawings - HWDT6648CHSS-S](#)  
[SDS - HCC\\_SDS](#)  
[Sell Sheets - T-CHSS Series Stainless Steel Wiring Trough](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WIEG-T6648CHSS-SPEC-EN | REV 1/2024