



NEMA 4X Hinge Cover Wire Trough 8 X 8 X 12 304 Stainless Steel

By Wiegmann
Catalog # [T8812CHSS](#)



NEMA 4X Hinge Cover Wire Trough 8 X 8 X 12 304 Stainless Steel

*Representative Image

Features

- Trough and cover are fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Easy to operate external clamps and continuous hinge are provided
- External mounting feet are included
- Cover is sealed with a poured in place gasket

General

Cover Type	Hinged Cover
EU RoHS Indicator	No
Finish Type	Grained Stainless Steel
Latches Type	External Clamps
Material	304 Stainless Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Series	T_CHSS
UPC	786725888733

Dimensions

Actual Depth	12.31 in
Actual Height	9.5 in
Actual Width	9.5 in
Depth	12 in
Height	8 in
Weight	13.7 lb
Width	8 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	1, 12, 4 & 4X

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - T8812CHSS](#)
- [Catalogs - Wiegmann Wireways & Fittings](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDT8812CHSS-S](#)
- [Sales Drawings - HWDT8812CHSS-S](#)
- [SDS - HCC_SDS](#)
- [Sell Sheets - T-CHSS Series Stainless Steel Wiring Trough](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.