



NEMA 4X Gasketed Screw Cover 6X6X4 316 Stainless Steel

By Wiegmann
Catalog # [WA060604GSCSSA](#)

NEMA 4X Gasketed Screw Cover 6X6X4 316 Stainless Steel



*Representative Image

Features

-
-
-
-
-

General

Application	Designed for use as a wiring box, junction box, pull box, or terminal box with many indoor and outdoor applications where dust or moisture is a problem.
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Smooth Grained
Material	316 Stainless Steel
Mounting Type	Wall
Number of Doors (Fixed)	1
UPC	786725890880

Dimensions

Actual Height	6.125 in
Actual Width	6.125 in
Cubic Capacity	144 cu.in
Depth	4 in
Height	6 in
Width	6 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4, 4X, 12, 13

Logistics

Carton Quantity 1 EA

Product Assets

- [3D Models - WA060604GSCSSA](#)
- [Catalogs - Wiegmann Stainless Steel & Aluminium](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDWA060604GSCSSA-S](#)
- [Engineering Drawing - HWDWA060604GSCSS-S](#)
- [Sales Drawings - HWDWA060604GSCSS-S](#)
- [Sales Drawings - HWDWA060604GSCSSA-S](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - NEMA 4X Stainless Steel Screw Cover Enclosures](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-WA060604GSCSSA-SPEC-EN | REV 6/2024