

**NEMA 4X Gasketed Screw Cover
8X8X6 316 Stainless Steel**

By Wiegmann
Catalog # [WA080806GSCSSA](#)

NEMA 4X Gasketed Screw Cover 8X8X6 316 Stainless Steel



*Representative Image

Features

- Bodies and covers are fabricated from 316 stainless steel
- Seams are continuously welded and ground smooth
- Cover contains a closed cell oil resistant neoprene gasket
- Ground stud is located on the inside of the cover
- No mounting provisions are provided

Application

Designed for use as a wiring box, junction box, pull box, or terminal box with many indoor and outdoor applications where dust or moisture is a problem.

General

Catalog Number	WA080806GSCSSA
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Smooth Grained
Material	316 Stainless Steel
Mounting Type	Wall
Number of Doors (Fixed)	1
UPC	786725890934

Dimensions

Actual Height	8.125 in
---------------	----------

Actual Width	8.125 in
Cubic Capacity	384 cu.in
Depth	6 in
Height	8 in
Width	8 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4, 4X, 12, 13

Logistics

Carton Quantity	1 EA
-----------------	------

Product Assets

- [3D Models - WA080806GSCSSA](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDWA080806GSCSSA-S](#)
- [Engineering Drawing - HWDWA080806GSCSS-S](#)
- [Sales Drawings - HWDWA080806GSCSS-S](#)
- [Sales Drawings - HWDWA080806GSCSSA-S](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - NEMA 4X Stainless Steel Screw Cover Enclosures](#)
- [Specifications - WA080806GSCSSA](#)
- [Terms and Conditions - HCC Terms & Conditions](#)